



USB-A to Lightning Sync/Charge Cable (M/M) - MFi Certified, Black, 6 ft. (1.8 m)

MODEL NUMBER: M100-006-BK











Highlights

- Reversible Lighting plug compatible with all devices with 8-pin connectors
- USB plug connects to USB-A port on computer or charger
- MFi-certified for use with iPhone, iPad and iPod devices

System Requirements

- Device or charger with USB-A port
- Most current iPhone, iPad and iPod devices

Package Includes

M100-006-BK USB-A to Lightning Sync/Charge Cable (M/M), Black, 6 ft. (1.8 m)

Charges and synchronizes your Apple iPhone, iPad or iPod using the USB port on your computer or wall/car charger.

Features

Helps You Charge and Sync Your Apple Mobile Device

The M100-006-BK connects your iPhone, iPad or iPod to the USB-A port on a computer or USB charger, so you can charge your Apple device and transfer data simultaneously. The reversible 8-pin Lightning plug connects in either direction to ensure fast, easy connection every time. The charging cable is MFicertified for broad compatibility with iPhone, iPad and iPod devices.

Specifications

OVERVIEW		
UPC Code	037332182166	
Technology	Lightning; USB 2.0 (High Speed)	
Cable Type	Passive	
INPUT		
Maximum Input Amps	2	
POWER		
USB Power Delivery (PD) Charging Support	No	
CONNECTIONS		
Side A - Connector 1	USB A (MALE)	
Side B - Connector 1	LIGHTNING (MALE)	





Connector Plating	Nickel	
Contact Plating	Gold	
Connector Style	Straight	
Connector dayle	Gragit	
CHARGING		
Total Charging Watts	12	
PLIVOIDAL		
PHYSICAL Material of Construction	DVC	
Material of Construction Cable Jacket Color	PVC Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	3.2mm 28/21	
Wire Gauge (AWG)		
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Cable Length (in.)	72	
Shipping Dimensions (hwd / in.)	5.30 x 1.00 x 2.60	
Shipping Dimensions (hwd / cm)	13.46 x 2.54 x 6.60	
Shipping Weight (lbs.)	0.10	
Shipping Weight (kg)	0.05	
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000	
Unit Packaging Type	Вох	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 176°F (-20° to 80°C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
Power Provided to Connected Device(s)	12W (5V/2.4A)	
FEATURES & SPECIFICATIONS		
USB Specification	USB 2.0 (up to 480 Mbps)	
Data Transfer Rate	480 Mbps	
Angled Plug	No	
STANDARDS & COMPLIANCE		





Product Certifications	MFi	
Product Compliance	RoHS; REACH; UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	2-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.