

USB-A to Lightning Sync/Charge Cables (M/M) - MFi Certified, Black, 10 in. (0.25 m), Pack of 10

MODEL NUMBER: M100-10N-BK-10



Charge and synchronize your Apple iPhone, iPad or iPod using the USB port on your computer or wall/car charger.

Features

Helps You Charge and Sync Your Apple Mobile Device

The M100-10N-BK-10 includes 10 M100-10N-BK sync/charge cables. They connect your iPhone, iPad or iPod to the USB-A port on a computer or USB charger, so you can charge your Apple device and transfer data simultaneously. The reversible 8-pin Lightning plug connects in either direction to ensure fast, easy connection every time. The charging cables are MFi-certified for broad compatibility with iPhone, iPad and iPod devices.

Specifications

OVERVIEW	
UPC Code	037332188526
Technology	Lightning; USB 2.0 (High Speed)
Cable Type	Passive
INPUT	
Maximum Input Amps	2
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Side A - Connector 1	USB A (MALE)

Highlights

- Includes ten M100-10N-BK charge/sync cables
- Reversible Lightning plugs compatible with all devices with 8-pin connectors
- USB plugs connect to USB-A port on computer or charger
- MFi-certified for use with iPhone, iPad and iPod devices

System Requirements

- Computer or charger with USB-A port
- Most current iPhone, iPad or iPod devices

Package Includes

(10) M100-10N-BK USB-A to Lightning Sync/Charge Cables (M/M), Black, 10 in. (0.25 m)



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	LIGHTNING (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
CHARGING	
Total Charging Watts	12
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	2.8mm
Wire Gauge (AWG)	30/24
Cable Length (ft.)	0.8
Cable Length (m)	0.24
Cable Length (in.)	10
Shipping Dimensions (hwd / in.)	1.25 x 2.80 x 5.25
Shipping Dimensions (hwd / cm)	3.18 x 7.11 x 13.34
Shipping Weight (lbs.)	0.26
Shipping Weight (kg)	0.12
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 176°F (-20° to 80°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	12W (5V/2.4A)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Data Transfer Rate	480 Mbps
Angled Plug	No



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	MFi
Product Compliance	RoHS; REACH; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.