



Powering Business Worldwide

3-ft. Gray Snagless Cat5e Molded Ethernet Cable

MODEL NUMBER: N001-003-GY-R



Description

Tripp Lite's 3-ft. gray snagless category 5e (Cat5e) patch cable has 2 snagless RJ45 molded male connectors featuring integral strain relief. The cable is manufactured from PVC 4-pair stranded UTP and is rated for 350MHz/1Gbps communication. All cables are offered in a variety of lengths and colors for all category 5 (Cat5) and 5e cabling needs. Standard category 5e patch cables are also available. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 3-ft. color: gray connectors: RJ45 male
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available without the snagless feature (N002 series)
- Also available - Cat6 cables (N201 series)
- Warranted to be free from defects in materials and workmanship for life.

Highlights

- Premium cabling for Category 5 and 5e applications; rated for 350 MHz/1 Gbps communications
- EEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors
- Retail packaging

System Requirements

- For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

Package Includes

- 3-ft. Gray Snagless Cat5e Patch Cable

Specifications

| OVERVIEW | |
|------------|--------------|
| UPC Code | 037332012456 |
| Technology | Cat5/5e |
| PHYSICAL | |



Powering Business Worldwide

| | |
|-------------------------------------|---------------------------|
| Color | Gray |
| Cable Shielding | UTP |
| Cable Length (ft.) | 3 |
| Cable Length (m) | 0.91 |
| Shipping Dimensions (hwd / in.) | 0.05 x 0.11 x 0.04 |
| Shipping Dimensions (hwd / cm) | 0.13 x 0.28 x 0.10 |
| Shipping Weight (lbs.) | 0.11 |
| Shipping Weight (kg) | 0.05 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.