



Cat5e 350 MHz Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), PoE - White, 3 ft. (0.91 m)

MODEL NUMBER: N001-003-WH



Description

This White snagless Cat5e Ethernet cable has two snagless RJ45 molded male connectors featuring integral strain relief. The cable is manufactured from PVC 4-pair solid UTP and is rated for 350 MHz/1 Gbps communication. All cables are offered in a variety of lengths and colors for all Cat5 and Cat5e cabling needs. Standard, non-snagless Cat5e cables are also available (N002-Series).

Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 3-ft. (0.91 m) color: White connectors: RJ45 male
- · Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available without the snagless feature (N002-Series)
- Also available Cat6 cables (N201-Series)

Specifications

OVERVIEW	
UPC Code	037332172471
Technology	Cat5/5e
POWER	

Highlights

- Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

System Requirements

 For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

Package Includes

• 3-ft. (0.91 m) White Snagless Cat5e Patch Cable





Power Over Cable (PoC) Support	No	
CONNECTIONS		
Side A - Connector 1	RJ45 (MALE)	
Side B - Connector 1	RJ45 (MALE)	
Crossover Wiring	No	
Contact Plating	Gold	
РоЕ Туре	Type 2 PoE+ (30W, IEEE 802.3at)	
Connector Type	Molded; Snagless	
Wiring Configuration	EIA/TIA 568B	
Angled Connector	No	
PHYSICAL		
Cable Jacket Color	White	
Cable Jacket Material	PVC	
Cable Jacket Rating	СМ	
Cable Shielding	UTP	
Cable Outer Diameter (OD)	5.0 mm	
Number of Conductors	4 Pair	
Conductor Material	Stranded Copper	
Conductor Gauge	26 AWG	
Cable Length (ft.)	3	
Cable Length (m)	0.91	
Cable Length (in.)	36	
Cable Length (cm)	91.4	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.09	
Shipping Weight (kg)	0.04	
ENVIRONMENTAL		
Operating Temperature Range	14° to 104°F (-10° to 40°C)	
Storage Temperature Range	5° to 122°F (-15° to 50°C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
COMMUNICATIONS		





Bandwidth per TIA Standard	100 MHz	
Maximum Bandwidth as Tested	350 MHz	
Network Compatibility	1 Gbps (Gigabit)	
IEEE Standards Supported	802.3ab; 802.3at	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
IP68 Rated	No	
Snagless Connector	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Certifications	UL Listed; cUL Listed	
Product Compliance	CE (Europe); RoHS; IEEE 802.3ab 1000Base-T; IEEE 802.3at PoE+; REACH; UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.