



Powering Business Worldwide

Cat5e 350 MHz Bulk Solid PVC Cable, Gray, 500 ft.

MODEL NUMBER: **N022-500-GY**



Description

Tripp Lite's 500-ft. gray category 5e (Cat5e) solid PVC bulk cable is designed for premise (in-wall) cabling applications. This 24 AWG 4-pair solid cable has a PVC jacket and is rated for 350MHz/1Gbps communication. Used for all non-plenum horizontal wiring applications. Meets most current industry standards including IEEE 802.3AB, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC11801 and ETL (category 5e draft 11). Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Designed for premise (in-wall) cabling applications
- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 500-ft. Color: gray
- 24 AWG 4-pair solid cable with PVC jacket
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other lengths
- Available in stranded copper cable (N020-01K-GY), in plenum cable (N024-01K) and in Cat6 (N222-01K and N224-01K)
- Warranted to be free from defects in materials and workmanship for life

Specifications

OVERVIEW	
UPC Code	037332013064
CONNECTIONS	
Side A - Connector 1	BARE WIRE

Highlights

- Premium cabling for Category 5 and 5e applications -- rated for 350 MHz/1Gbps communications

System Requirements

- For all non-Plenum horizontal premise (in-wall) wiring applications for Network Installations 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications.

Package Includes

- 500-ft. Cat5e Gray Bulk Patch Cable Solid PVC 24AWG 350MHz



Powering Business Worldwide

Side B - Connector 1	BARE WIRE
PHYSICAL	
Color	Gray
Cable Shielding	UTP
Cable Length (ft.)	500
Cable Length (m)	152.44
Shipping Dimensions (hwd / in.)	7.00 x 11.25 x 11.50
Shipping Dimensions (hwd / cm)	17.78 x 28.58 x 29.21
Shipping Weight (lbs.)	12.46
Shipping Weight (kg)	5.65
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.