



Cat5e 350 MHz Solid Core Outdoor-Rated (UTP) PVC Bulk Ethernet Cable, PoE - Gray, 1000 ft. (304.8 m)

MODEL NUMBER: N028-01K-GY



Highlights

- UV Rated jacket prevents drying and cracking
- 4PR Solid conductors for Low Attenuation Loss
- CMX Outdoor rating; Temp range -40F to +140F

Package Includes

1000ft. Box Cat5e Outdoor Rated PVC Bulk Cable

Features

- UV Rated jacket prevents drying and cracking
- 4PR Solid conductors for Low Attenuation Loss
- CMX Outdoor rating; Temp range: -40F to +140F
- 1000-ft. Pull-box, length marked every two feet
- Terminate with N030-010 Solid wire Cat5e RJ45 plugs

Specifications

OVEDVIEW.		
OVERVIEW		
UPC Code	037332141491	
Technology	Cat5/5e	
POWER		
Power Over Cable (PoC) Support	No	
CONNECTIONS		
Side A - Connector 1	BARE WIRE	
Side B - Connector 1	BARE WIRE	
Crossover Wiring	No	
Contact Plating	Gold	
PoE Type	Type 2 PoE+ (30W, IEEE 802.3at)	





Connector Type	Molded	
Wiring Configuration	EIA/TIA 568B	
Angled Connector	No	
PHYSICAL		
Cable Jacket Color	Gray	
Cable Jacket Material	PVC	
Cable Jacket Rating	CMR; CMX	
Cable Shielding	UTP	
Cable Outer Diameter (OD)	5.5 mm	
Number of Conductors	4 Pair	
Conductor Material	Solid Copper	
Conductor Gauge	24 AWG	
Cable Length (ft.)	1000	
Cable Length (m)	304.88	
Cable Length (in.)	12000	
Cable Length (cm)	30480	
Shipping Dimensions (hwd / in.)	9.00 x 14.60 x 15.00	
Shipping Dimensions (hwd / cm)	22.86 x 37.08 x 38.10	
Shipping Weight (lbs.)	24.90	
Shipping Weight (kg)	11.29	
ENVIRONMENTAL		
Operating Temperature Range	14° to 104°F (-10° to 40°C)	
Storage Temperature Range	5° to 122°F (-15° to 50°C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
COMMUNICATIONS		
Bandwidth per TIA Standard	100 MHz	
Maximum Bandwidth as Tested	350 MHz	
Network Compatibility	1 Gbps (Gigabit)	
IEEE Standards Supported	802.3ab; 802.3at	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
IP68 Rated	No	





Snagless Connector	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Certifications	UL Listed; cUL Listed	
Product Compliance	CE (Europe); RoHS; IEEE 802.3ab 1000Base-T; IEEE 802.3at PoE+; REACH; UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.