



Cat6 Gigabit Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), PoE, Yellow, 4 ft. (1.22 m)

MODEL NUMBER: N201-004-YW





Features

- Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- Length: 4 ft./Color: Yellow/Connectors: RJ45 male
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Deliver stable performance up to 550MHz/1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- Available in other colors and lengths

Highlights

- Premium cabling for Category 6, Category 5e and Category 5 applications—rated for 550 MHz/1 Gbps communications
- Designed to meet Category 6 specifications; reduces crosstalk and return loss
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

System Requirements

 For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.

Package Includes

 4-ft. Cat6 Yellow Gigabit Patch Cord Snagless Molded

Specifications

| OVERVIEW | | |
|----------------------|--------------|--|
| UPC Code | 037332158772 | |
| Technology | Cat6; PoE | |
| CONNECTIONS | | |
| Side A - Connector 1 | RJ45 (MALE) | |
| Side B - Connector 1 | RJ45 (MALE) | |
| Crossover Wiring | No | |





| Contact Plating | Gold | |
|---------------------------------|---------------------------------|--|
| PoE Type | Type 2 PoE+ (30W, IEEE 802.3at) | |
| Connector Type | Snagless; Molded | |
| Wiring Configuration | EIA/TIA 568B | |
| Angled Connector | No | |
| PHYSICAL | | |
| Cable Jacket Color | Yellow | |
| Cable Jacket Material | PVC | |
| Cable Jacket Rating | СМ | |
| Cable Shielding | UTP | |
| Cable Outer Diameter (OD) | 6.0 mm | |
| Number of Conductors | 4 Pair | |
| Conductor Material | Stranded Copper | |
| Conductor Gauge | 24 AWG | |
| Cable Length (ft.) | 4 | |
| Cable Length (m) | 1.22 | |
| Cable Length (in.) | 48 | |
| Cable Length (cm) | 121.9 | |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 | |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 | |
| Shipping Weight (lbs.) | 0.13 | |
| Shipping Weight (kg) | 0.06 | |
| Unit Dimensions (hwd / in.) | 0.000 x 0.000 x 0.000 | |
| ENVIRONMENTAL | | |
| Operating Temperature Range | 14° to 122°F (-10° to 50°C) | |
| Storage Temperature Range | 5° to 140°F (-15° to 60°C) | |
| Operating Humidity Range | 0% to 90% RH, Non-Condensing | |
| Storage Humidity Range | 0% to 90% RH, Non-Condensing | |
| COMMUNICATIONS | | |
| Bandwidth per TIA Standard | 250 MHz | |
| Maximum Bandwidth as Tested | 500 MHz | |
| Network Compatibility | 1 Gbps (Gigabit) | |
| IEEE Standards Supported | 802.3an; 802.3at | |
| · | • | |





| FEATURES & SPECIFICATIONS | | |
|--|---|--|
| Antibacterial | No | |
| IP68 Rated | No | |
| Snagless Connector | Yes | |
| IP20 Rated | No | |
| STANDARDS & COMPLIANCE | | |
| Product Certifications | UL Listed; cUL Listed | |
| Product Compliance | CE (Europe); RoHS; IEEE 802.3an 10GBase-T; IEEE 802.3at PoE+; REACH; UKCA | |
| WARRANTY & SUPPORT | | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty | |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.