



# Cat6 Gigabit Snagless Molded Plenum-Rated (UTP) Ethernet Cable, (RJ45 M/M), PoE, Gray, 50 ft. (15.24 m)

## MODEL NUMBER: N201-050-GY-P



### Features

- CMP plenum-rated, pre-terminated Cat6 patch cable
- Protective, flexible boot
- Cat6-rated "staggered" RJ45 plugs for greatly reduced NEXT

## **Specifications**

| OVERVIEW             |                                 |  |
|----------------------|---------------------------------|--|
| UPC Code             | 037332141170                    |  |
| Technology           | Cat6; PoE                       |  |
| CONNECTIONS          |                                 |  |
| Side A - Connector 1 | RJ45 (MALE)                     |  |
| Side B - Connector 1 | RJ45 (MALE)                     |  |
| Crossover Wiring     | No                              |  |
| Contact Plating      | Gold                            |  |
| РоЕ Туре             | Type 2 PoE+ (30W, IEEE 802.3at) |  |
| Connector Type       | Snagless; Molded                |  |
| Wiring Configuration | EIA/TIA 568B                    |  |
| Angled Connector     | No                              |  |
| PHYSICAL             |                                 |  |

## **Highlights**

- CMP plenum-rated gray Cat6 cable - 50-ft. (15.24 m)
- For use in walls or ceilings where fire codes dictate plenum rated cabling
- Pliable snagless boot protects RJ45 tab when pulling through ceilings, etc.

#### **Package Includes**

• 50-ft. (15.24 m) Cat6 Gray Gigabit Plenum Snagless Patch Cable





| [                               |   |
|---------------------------------|---|
| Cable Jacket Color              | Gray  |
| Cable Jacket Material           | PVC   |
| Cable Jacket Rating             | СМР   |
| Cable Shielding                 | UTP   |
| Cable Outer Diameter (OD)       | 5.7 mm  |
| Number of Conductors            | 4 Pair  |
| Conductor Material              | Solid Copper  |
| Conductor Gauge                 | 24 AWG  |
| Cable Length (ft.)              | 50  |
| Cable Length (m)                | 15.24   |
| Cable Length (in.)              | 600   |
| Cable Length (cm)               | 1524  |
| Shipping Dimensions (hwd / in.) | 12.00 x 10.00 x 0.50  |
| Shipping Dimensions (hwd / cm)  | 30.48 x 25.40 x 1.27  |
| Shipping Weight (lbs.)          | 1.30  |
| Shipping Weight (kg)            | 0.59  |
| ENVIRONMENTAL                   |   |
| Operating Temperature Range     | 14° to 122°F (-10° to 50°C)   |
| Storage Temperature Range       | 5° to 140°F (-15° to 60°C)  |
| Operating Humidity Range        | 0% to 90% RH, Non-Condensing  |
| Storage Humidity Range          | 0% to 90% RH, Non-Condensing  |
| COMMUNICATIONS                  |   |
| Bandwidth per TIA Standard      | 250 MHz   |
| Maximum Bandwidth as Tested     | 500 MHz   |
| Network Compatibility           | 1 Gbps (Gigabit)  |
| IEEE Standards Supported        | 802.3an; 802.3at  |
| FEATURES & SPECIFICATIONS       |   |
| Antibacterial                   | No  |
| IP68 Rated                      | No  |
| Snagless Connector              | Yes   |
| STANDARDS & COMPLIANCE          |   |
| Product Certifications          | UL Listed; cUL Listed   |
| Product Compliance              | CE (Europe); RoHS; IEEE 802.3an 10GBase-T; IEEE 802.3at PoE+; REACH; UKCA |
|                                 |   |



United States

https://tripplite.eaton.com



| WARRANTY & SUPPORT                     |   |  |  |
|--|---|--|--|
| Product Warranty Period<br>(Worldwide) | Lifetime limited warranty                             |  |  |
|  |   |  |  |
| 1000 Eaton Boulevard                   | © 2024 Eaton. All Rights Reserved.                    |  |  |
| Cleveland, OH 44122                    | Eaton is a registered trademark. All other trademarks |  |  |

are the property of their respective owners.