

Cat6 Gigabit Snagless Molded Plenum-Rated (UTP) Ethernet Cable, (RJ45 M/M), PoE, Gray, 100 ft. (30.5 m)

MODEL NUMBER: N201-100-GY-P



Highlights

- CMP plenum-rated gray Cat6 patch cable
- For use in walls or ceilings where fire codes dictate plenum-rated cabling
- Pliable snagless boot protects RJ45 tab when pulling through ceilings, etc.

Package Includes

- 100-ft. (30.5 m) Cat6 Gray Gigabit Plenum Snagless Patch Cable

Features

- CMP plenum-rated, pre-terminated Cat6 patch cable
- Protective, flexible boot
- Cat6 rated "staggered" RJ45 plugs for greatly reduced NEXT

Specifications

OVERVIEW	
UPC Code	037332141118
Technology	Cat6; PoE
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Crossover Wiring	No
Contact Plating	Gold
PoE Type	Type 2 PoE+ (30W, IEEE 802.3at)
Connector Type	Snagless; Molded
Wiring Configuration	EIA/TIA 568B
Angled Connector	No
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Jacket Color	Gray
Cable Jacket Material	PVC
Cable Jacket Rating	CMP
Cable Shielding	UTP
Cable Outer Diameter (OD)	5.7 mm
Number of Conductors	4 Pair
Conductor Material	Solid Copper
Conductor Gauge	24 AWG
Cable Length (ft.)	100
Cable Length (m)	30.49
Cable Length (in.)	1200
Cable Length (cm)	3048
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 0.50
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 1.27
Shipping Weight (lbs.)	2.65
Shipping Weight (kg)	1.20
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
Bandwidth per TIA Standard	250 MHz
Maximum Bandwidth as Tested	500 MHz
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3an; 802.3at
FEATURES & SPECIFICATIONS	
Antibacterial	No
IP68 Rated	No
Snagless Connector	Yes
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cUL Listed
Product Compliance	CE (Europe); RoHS; IEEE 802.3an 10GBase-T; IEEE 802.3at PoE+; REACH; UKCA



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.