

10GBase CX4 Cable, 10M (33-ft.)

MODEL NUMBER: N263-10M



Highlights

- 10 Meter CX4 Cable
- Works with any manufacturers' 10Gb XenPak
- Made with Premium Madison TurboTwin™ cable
- Compliant with the IEEE Draft specification P802.3ak/D5.3

System Requirements

- Ethernet switches with CX4 / Xenpak modules for 10Gbps linking

Package Includes

10 GBase CX4 Cable (10 Meter)

Description

Tripp Lite's high-speed 10Gbps CX4 Cables provide an ultra high-performance, cost-effective solution for Gigabit Copper applications. Featuring 26AWG Madison TurboTwin™ twinaxial cable, these cables utilize up to 3.125 gigabytes per second wire speed connections with four channels. Cables work with any manufacturers' 10Gbps Xenpak transceivers that utilize the Ejector style latch connector. Tripp Lite CX4 cables are also available in 0.5 meter, 1 meter, 3 meter, and 5 Meter lengths.

Features

- 10 Meter CX4 Cable
- Flexible 26AWG Madison TurboTwin™ Cable
- Ejector style latch mechanism
- Connects the CX4 modules between two switches
- Fully 802.3ak compliant
- RoHS Compliant

Specifications

OVERVIEW	
UPC Code	037332177384
CONNECTIONS	
Side A - Connector 1	CX4 [SFF-8470] (MALE)
Side B - Connector 1	CX4 [SFF-8470] (MALE)
Angled Connector	No



Powering Business Worldwide



PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	32.8
Cable Length (m)	10.00
Cable Length (in.)	393.6
Shipping Dimensions (hwd / in.)	10.00 x 12.00 x 0.10
Shipping Dimensions (hwd / cm)	25.40 x 30.48 x 0.25
Shipping Weight (lbs.)	2.50
Shipping Weight (kg)	1.13
FEATURES & SPECIFICATIONS	
Antibacterial	No
IP68 Rated	No
Snagless Connector	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.