




# Duplex Singlemode 9/125 Fiber Patch Cable (LC to SC/APC), 2M (6 ft.)

## MODEL NUMBER: N366-02M-AP



## Features

- LC to SC/APC (Angle Physical Contact), 2 Meter Fiber Patch cable
- Manufactured from 9/125 duplex (zipcord) fiber
- PVC jacket
- Length: 1-meter. Connectors: 2 SC (Green ) and 2 LC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

## **Specifications**

OVERVIEW	
UPC Code	037332150967
Technology	Singlemode
Optical Mode	OS2
CONNECTIONS	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	SC DUPLEX (MALE)
Endface Polish	APC; UPC
PHYSICAL	

## **Highlights**

- LC to SC/APC (Angle Physical Contact), 2 Meter Fiber Patch cable
- Premium PVC 9/125 micron singlemode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Twice the bandwidth throughput of multimode cable

#### **Package Includes**

 2 Meter (6-ft.) Duplex SMF 9/125 Patch Cable, LC to SC/APC





WARRANTY & SUPPORT	
Product Compliance	RoHS; REACH
STANDARDS & COMPLIANCE	
Trunk	No
Breakout	No
Push/Pull Tabs	No
FEATURES & SPECIFICATIONS	
Insertion Loss	0.30 dB
Attenuation @ 1550NM	0.22 dB/km
Attenuation @ 1310NM	0.36 dB/km
Network Compatibility	1 Gbps (Gigabit); 10 Gbps; 25 Gbps; 40 Gbps; 100 Gbps; 400 Gbps
COMMUNICATIONS	
Storage Humidity Range	35% to 65% RH, Non-Condensing
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
ENVIRONMENTAL	
Fiber Cable Length	2M (6.6 ft)
Shipping Weight (kg)	0.03
Shipping Weight (lbs.)	0.06
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)
Cable Length (in.)	78.7
Cable Length (m)	2.01
Cable Length (ft.)	6.6
Number of Fibers	2
Core Diameter (microns)	9
Clad Diameter (microns)	125
Cable Jacket Rating	OFNR
Cable Jacket Material	LSZH
Connector Color	Green; Blue; White
Cable Jacket Color	Yellow





Product Warranty Period (Worldwide)

Lifetime limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.