

Duplex Multimode 62.5/125 Fiber Adapter (LC-ST M/F) 1 ft. (0.31 m)

MODEL NUMBER: N457-001-62



Highlights

- Utilize Existing SC or ST Cabling with new LC type switches
- Available in 62.5/125 or 50/125 Micro
- LC/ST or LC/SC

Package Includes

- LC/ST Duplex Multimode 62.5/125 Male-Female Fiber Adapter Cable, 1-ft. (0.31 m)

Features

- Save money by utilizing older, existing fiber ST or SC cables with new LC installations
- Available in LC/ST or LC/SC in both 62.5/125 and 50/125 micron

Specifications

OVERVIEW	
UPC Code	037332135384
Technology	Multimode
CONNECTIONS	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	ST DUPLEX (FEMALE)
PHYSICAL	
Color	Orange
Cable Jacket Material	LSZH
Cable Jacket Rating	OFNR
Clad Diameter (microns)	125
Core Diameter (microns)	62.5
Number of Fibers	2
Cable Length (ft.)	1



Powering Business Worldwide



Cable Length (m)	0.30
Cable Length (in.)	12
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
FEATURES & SPECIFICATIONS	
Push/Pull Tabs	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.