

Copper/Fiber Enclosure for 4 High-Density Cassettes, 1U

MODEL NUMBER: **N484-01U**



Description

The N484-01U is a 19-inch rack-mount chassis that supports up to four high-density copper/fiber cassettes for managing your networking equipment in 1U of space. Choose among a wide array of cassettes ranging from LC and MTP fiber to SFP+ and RJ45 copper. Fiber cassettes come in multiple variations, allowing you to connect and interconnect your 10 Gb, 40 Gb and 100/120 Gb equipment. The N484-12SFP-K is an innovative 12-port passive SFP+ hub cassette that comes with six QSFP+ to (x4) SFP+ breakout cables, allowing for distributed redundancy between multiple 40 Gb devices. The N484-01U is a solution that is well suited for SME (Small and Medium Enterprise) and other applications where equipment is being connected in one to three adjacent racks. In addition, this unique chassis allows for seamless flexibility to connect to existing cabling infrastructure. Add up to 48 ports of Duplex LC, MTP, Cat5e/6 RJ45 or SFP+.

Features

- Space saving 1U, 19" rackmountable design supports up to 4 High Density Copper / Fiber cassettes
- Choose amongst a wide array of cassettes ranging from LC and MTP fiber to SFP+ and RJ45 copper, all in a single 1U chassis
- Fiber cassettes allow for the connection and interconnection of 10Gb, 40Gb, and 100/120Gb equipment
- The N484-12SFP-K Passive SFP+ hub cassette is an innovative solution that allows for distributed redundancy between multiple 40Gb devices
- Fully passive, no added heat or cooling load
- Features a fold-down door panel on the front of the unit that protects your connections, while rotating out of the way to provide full access. Door panel can also be removed altogether.
- Fold-down door panel opens 180° to reveal labels for cable routing information
- Includes optional rear-mounting cable management bracket for proper routing of cabling
- Manufactured with heavy duty, 1.0mm Cold Rolled Steel

Highlights

- Space saving 1U, 19" rackmountable design supports up to 4 High Density Copper / Fiber cassettes
- Choose amongst a wide array of cassettes ranging from LC and MTP fiber to SFP+ and RJ45 copper, all in a single 1U chassis
- Fiber cassettes allow for the connection and interconnection of 10Gb, 40Gb, and 100/120Gb equipment
- The N484-12SFP-K Passive SFP+ hub cassette is an innovative solution that allows for distributed redundancy between multiple 40Gb devices
- Fully passive; no added heat or cooling load

Package Includes

- High Density Copper / Fiber Enclosure Panel, 1U, 4-Cassette Capacity
- Quick Start Guide

Specifications

OVERVIEW

UPC Code

037332187239



Powering Business Worldwide

TRIPP LITE
SERIES

Accessory Type	Pass-Through Panel
Technology	Cat5/5e; Cat6; Cat6a; Multimode
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	14.96 x 21.30 x 3.54
Shipping Dimensions (hwd / cm)	38.00 x 54.10 x 8.99
Shipping Weight (lbs.)	6.39
Shipping Weight (kg)	2.90
Unit Dimensions (hwd / in.)	1.750 x 21.260 x 19.000
Unit Weight (lbs.)	4.4
Unit Weight (kg)	2.00
Panel Style	Cassette Type
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.