



16-Port Fiber Patch Panel, 1U (ST/ST), Multimode or Singlemode

MODEL NUMBER: N490-016-STST



Description

This 16-port 1U rack-mount ST/ST Fiber Optic Patch Panel provides efficient and easy management of fiber optic cables in the rack or cabinet. Pre-loaded, feed-through duplex multimode connectors are mounted on a 16-gauge, cold-rolled, black powder-coated steel panel. Use with 62.5/125 or 50/125 Multimode or 9/125 Singlemode fiber Ethernet cables. Panel measures 19 inches wide by 1.75 inches high.

Features

- 16 ports ST/ST
- Only 1U of rack-space
- Use with 62.5/125 or 50/125 Multimode, or 9/125 Singlemode fiber patch cables
- Available in ST/ST, SC/SC, LC/LC,

Specifications

OVERVIEW	
UPC Code	037332135346
Product Type	Feed-Through
Technology	Multimode
CONNECTIONS	
Number of Ports	16
Side A - Connector 1	ST DUPLEX (FEMALE)
Side B - Connector 1	ST DUPLEX (FEMALE)
PHYSICAL	

Highlights

- Simplified Fiber Optic Patching
- Multimode 62.5/125 or 50/125, Singlemode 9/125
- 16 ports in 1U of rackspace

Package Includes

 16 Port ST/ST Duplex Multimode or Singlemode Fiber Optic Patch Panel





3.90 x 3.10 x 21.80	
9.91 x 7.87 x 55.37	
1.00	
0.45	
Pass-Through	
COMMUNICATIONS	
0.1 dB	
STANDARDS & COMPLIANCE	
RoHS	
WARRANTY & SUPPORT	
Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.