



Important Note

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks. **10Gb Duplex Multimode 50/125 OM3 LSZH Fiber Patch Cable (LC/SC) - Aqua, 2M (6 ft.)**

MODEL NUMBER: N816-02M



Features

- 2 Meter LC/SC 10Gb 50/125 Aqua Fiber Patch Cable, OM3 Rated
- 10gb Ethernet speed to 300 meters @850nm
- Use with VCSEL and LED laser light sources
- High-Speed, High-Bandwidth, Low-Cost
- Backward compatible with legacy LAN's
- Ideal for Fibre Channel (SAN) applications
- IEEE 802.3ae and TIA LOMMF compliant

Specifications

OVERVIEW		
UPC Code	037332139764	
Technology	Multimode	
Optical Mode	OM3	
CONNECTIONS		
Side A - Connector 1	SC DUPLEX (MALE)	
Side B - Connector 1	LC DUPLEX (MALE)	
Endface Polish	PC	

Highlights

- 2 Meter LC/SC 10Gb 50/125 Aqua Fiber Patch Cable...OM3 Rated
- Designed for 10-Gig Ethernet
 applications
- Backward compatible with existing 50/125 fiber
- Max 10Gb distance of 300 meters @850nm
- Low-Smoke, Zero Halogen (LSZH) Aqua jacket

Package Includes

2 meter (6.5 ft) Duplex Multimode 50/125 Aqua OM3 Fiber Patch Cable, SC/LC





PHYSICAL		
Cable Jacket Color	Aqua	
Connector Color	White; Beige	
Cable Jacket Material	LSZH	
Cable Jacket Rating	OFNR	
Clad Diameter (microns)	125	
Core Diameter (microns)	50	
Number of Fibers	2	
Cable Length (ft.)	6.6	
Cable Length (m)	2.01	
Cable Length (in.)	78.7	
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)	
Shipping Dimensions (hwd / in.)	0.25 x 6.00 x 7.00	
Shipping Dimensions (hwd / cm)	0.64 x 15.24 x 17.78	
Shipping Weight (lbs.)	0.05	
Shipping Weight (kg)	0.02	
Fiber Cable Length	2M (6.6 ft)	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	5% to 85% RH, Non-Condensing	
Storage Humidity Range	35% to 65% RH, Non-Condensing	
COMMUNICATIONS		
Network Compatibility	1 Gbps (Gigabit); 10 Gbps; 25 Gbps; 40 Gbps; 100 Gbps	
Attenuation @ 850NM	3.0 dB/km	
Insertion Loss	LC 0.20 dB; SC 0.20 dB	
FEATURES & SPECIFICATIONS		
Push/Pull Tabs	No	
Breakout	No	
Trunk	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; REACH	



United States

https://tripplite.eaton.com



WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
1000 Eaton Boulevard	© 2024 Eaton. All Rights Reserved.	
Cleveland, OH 44122	Eaton is a registered trademark. All other trademarks	

are the property of their respective owners.