

Heavy-Duty Power Extension Cord, 20A, 12AWG (Left Angle IEC-320-C19 to IEC-320-C20), 2-ft.

MODEL NUMBER: P036-002-19LA



Highlights

- C19 Left Angle to C20 Power Cord, 2 ft.
- 12AWG (3.31mm²) x 3C, 20 Amp Rated, 100-250V
- RoHS Approved

Package Includes

C19 Left Angle to C20 Power Cable, 2 ft.

Description

Use Tripp Lite's P036-002-19LA in server applications that require a higher rated, heavier gauge cable. C19 Left Angle to C20 connectors, 3 x 12ga (3.31mm²) conductors, 20AMP rated, 100-250V - ideal for use with Blade Server Chassis.

Features

- Molded, Heavy-Duty Power Cord, 2 ft.
- IEC-60320-C19 Left Angle to IEC-60320-C20
- 12AWG (3.31mm²) x 3C, SJTW, 20A, 100-250V
- RoHS Approved

Specifications

OVERVIEW	
UPC Code	037332156501
CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C19 - LEFT ANGLE
PHYSICAL	
Color	Black
Power Cord Jacket Type	SJTW
Wire Gauge (AWG)	12



Powering Business Worldwide



Wire Gauge (OD - mm ²)	3.31mm ²
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	6.00 x 7.80 x 9.40
Shipping Dimensions (hwd / cm)	15.24 x 19.81 x 23.88
Shipping Weight (lbs.)	5.20
Shipping Weight (kg)	2.36
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.