

# Heavy-Duty Power Extension Cord, 20A, 12AWG (Right Angle IEC-320-C19 to IEC-320-C20), 2-ft.

MODEL NUMBER: P036-002-19RA



### Highlights

- C19 Right Angle to C20 Power Cord, 2 ft.
- 12AWG (3.31mm<sup>2</sup>) x 3C, 20 Amp Rated, 100-250V
- RoHS Approved

### Package Includes

- C19 Right Angle to C20 Power Cord, 2 ft.

### Description

Use Tripp Lite's P036-002 in server applications that require a higher rated, heavier gauge cable. C19 Right Angle to C20 connectors, 3 x 12ga (3.31mm<sup>2</sup>) conductors, 20AMP rated, 100-250V - ideal for use with Blade Server Chassis.

### Features

- Molded, Heavy-Duty Power Cord, 2 ft.
- IEC-60320-C19 Right Angle to IEC-60320-C20
- 12AWG (3.31mm<sup>2</sup>) x 3C, SJTW, 20A, 100-250Volt
- RoHS Approved

## Specifications

OVERVIEW	
UPC Code	037332156518
CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C19 - RIGHT ANGLE
PHYSICAL	
Color	Black
Power Cord Jacket Type	SJTW
Wire Gauge (AWG)	12



Powering Business Worldwide



Wire Gauge (OD - mm <sup>2</sup> )	3.31mm <sup>2</sup>
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	0.25 x 5.20 x 10.80
Shipping Dimensions (hwd / cm)	0.64 x 13.21 x 27.43
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.