

UK Computer Power Cord, C19 to BS1363, 13A, 250V, 16 AWG, 8 ft. (2.43 m), Black

MODEL NUMBER: P052-008



UK power cord delivers electricity from a BS 1363 wall outlet to a network device with a C20 inlet, such as a blade server, PDU or UPS.

Features

UK IEC Power Cord with C19 to BS 1363 Connection for Powering Network Devices This BS 1363 power cord is designed for blade server chassis, switches, routers, PDUs, UPS systems and other network devices. It features a BS 1363 plug for connecting to a wall outlet and a C19 plug for connecting to a device. The 8-ft. (2.43 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering switches and other network devices
- BS 1363 plug connects to AC power; C19 plug connects to device's C20 inlet
- UK power cable is ideal replacement for worn-out or missing cord
- 8-ft. (2.43 m) length allows you greater freedom in placing devices away from outlet

Applications

- Connect network devices like blade server chassis, switches, PDUs and UPS systems to a power outlet up to 2.4 m away in your data center
- Extend an existing power connection up to 2.4 m to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P052-008 UK Power Cable with BS 1363 Plug, 8-ft. (2.43 m), Black

Specifications

OVERVIEW	
UPC Code	037332141996
Device Compatibility	Server; Router; Network Switch; UPS; PDU
Country/Region	UK
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	BS1363 UK PLUG
Side B - Connector 1	IEC-320-C19



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.4mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.29
Cable Length (ft.)	8
Cable Length (m)	2.44
Shipping Dimensions (hwd / in.)	0.25 x 5.70 x 6.90
Shipping Dimensions (hwd / cm)	0.64 x 14.48 x 17.53
Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
Unit Dimensions (hwd / in.)	0.250 x 5.700 x 6.900
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	35% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.