

# Keyspan Mini DisplayPort to HDMI Active Adapter Video Converter (M/F) - 4K, DP1.2, 6 in.

MODEL NUMBER: P137-06N-HD-UHD



Connect a UHD 4K x 2K HDMI monitor to a Mac or PC with a Mini Displayport output

## Features

- Connect a UHD HDMI TV to a Mac or PC with a Mini Displayport output
- Active adapter for use with any Mini Displayport (or Thunderbolt 1 & 2) port
- Converts Single-Mode and Dual-Mode (DP++) Mini DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals
- Plug-and-play operation with no software required for easy, immediate installation
- Supports Ultra High Definition (UHD) video resolutions up to 4K x 2K (3840 x 2160) @ 24/30 Hz
- HDCP compliant
- Transmits an audio signal as long as it is supported by the Mini DisplayPort; check the documentation for your Mini DisplayPort source for compatibility

## Highlights

- Connect a UHD HDMI monitor to a Mac or PC with a Mini Displayport output
- Active adapter for use with any Mini Displayport (or Thunderbolt 1 & 2) port
- Plug-and-play convenience—no drivers or software needed
- Supports Ultra High Definition (UHD) video resolutions up to 4Kx2K, 3840 x 2160 (24Hz or 30Hz)
- HDCP compliant

## System Requirements

- Computer with a Mini DisplayPort (or Thunderbolt 1 & 2) port
- Monitor with a HDMI port
- 7.1 Audio Surround Sound is supported as long as it is supported by the source. Check your Mini DisplayPort source documentation for compatibility.
- Requires that the connected computer has a DP++ ( DisplayPort ++ ) port, which allows HDMI and DVI signals to be passed through. Check your Mini DisplayPort source documentation for compatibility.

## Package Includes

- P137-06N-HD-UHD Keyspan Mini DisplayPort 1.2 to UHD 4K HDMI Active Adapter/Video Converter (M/F), 6 in.

## Specifications

OVERVIEW	
UPC Code	037332183910
Product Type	Video Adapter
Technology	HDMI; DisplayPort
VIDEO	
Max Supported Color Depth	36-bit Deep Color
CONNECTIONS	



Powering Business Worldwide



Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
<b>PHYSICAL</b>	
Color	White
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	9.00 x 0.50 x 7.00
Shipping Dimensions (hwd / cm)	22.86 x 1.27 x 17.78
Shipping Weight (lbs.)	0.26
Shipping Weight (kg)	0.12
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.