



Mini DVI to VGA Cable Adapter, Video Converter for Macbooks and iMacs (M/F)

MODEL NUMBER: P138-000-VGA



Highlights

- Connect a VGA Monitor to an Apple Intel iMac, MacBook, or 12-inch PowerBook G4 mini-DVI Port
- 8-inch overall length

System Requirements

 Apple Intel iMac, MacBook, or 12-inch PowerBook G4

Package Includes

8-inch mini-DVI to VGA Adapter

Description

This Mini-DVI to VGA Female Video Adapter Cable allows you to connect a VGA display to the mini-DVI port found on some Apple computer models. Supports resolutions up to 1920 x 1080 (1080i).

Features

- Connect a VGA Monitor to an Apple Intel iMac, MacBook, or 12-inch PowerBook G4 mini-DVI Port
- 8-inch overall length
- Supports video resolutions up to 1920 x 1080 (1080i)

Specifications

OVERVIEW		
UPC Code	037332176752	
Product Type	Video Adapter	
Technology	DVI; VGA/SVGA	
CONNECTIONS		
Side A - Connector 1	MINI-DVI (MALE)	
Side B - Connector 1	HD15 (FEMALE)	
PHYSICAL		
Color	White	
Cable Jacket Color	White	
Cable Length (ft.)	0.7	





Cable Length (m)	0.21	
Cable Length (in.)	8	
Cable Length (cm)	20.32	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Weight (lbs.)	0.13	
Shipping Weight (kg)	0.06	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.