



Keyspan Mini DisplayPort to DisplayPort Cable Adapter, Video Converter (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P139-06N-DP



Highlights

- Converts Mini Displayport on a MAC to Displayport Female
- Connect Displayport enabled monitor to a MAC computer
- Supports resolutions up to 2560 x 1600 @ 60Hz

Package Includes

6-inch Mini Displayport Male to Displayport Female Adapter

Features

- Connect a Displayport enabled Monitor to a MAC Mini-Displayport video port
- Plug and Play no drivers or setup needed
- Displayport 1.1a Compliant
- HDCP Compliant
- Supports resolutions up to 2560 x 1600 @ 60Hz

Specifications

OVERVIEW		
UPC Code	037332161277	
Product Type	Video Adapter	
Technology	DisplayPort	
CONNECTIONS		
Side A - Connector 1	MINI DISPLAYPORT (MALE)	
Side B - Connector 1	DISPLAYPORT (FEMALE)	
PHYSICAL		
Color	White	
Cable Jacket Color	White	
Cable Length (ft.)	0.5	
Cable Length (m)	0.15	





Shipping Dimensions (hwd / in.)	0.25 x 0.25 x 6.50	
Shipping Dimensions (hwd / cm)	0.64 x 0.64 x 16.51	
Shipping Weight (lbs.)	0.05	
Shipping Weight (kg)	0.02	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.