



HDMI Display-Side Wallplate with Active Signal Booster, White (F/F)

MODEL NUMBER: P166-001-A









Highlights

- Extend a 1080p (24Hz) HDMI signal up to 150-ft. (45.72 m) from the source
- When extending a 1080p (24Hz) signal more than 75-ft. (22.86 m), use cable made with 24Awg wiring, such as the P568-100-HD
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50-ft. (15.24 m). A 3D signal can be extended up to 125-ft. (38.1 m) using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio

Package Includes

 HDMI Display-side Wallplate w/Signal Booster

Description

Tripp Lite's P166-001-A HDMI Display-side Wallplate with Signal Booster increases the distance a 1080p (24Hz) signal can be transmitted beyond the recommended 16-ft. (4.88 m.). It supports video resolutions up to 1080p, and a maximum distance of 150-ft. (45.72 m) from the source. Use P568-Series HDMI cables in most applications. When extending a 1080p (24Hz) signal more than 75-ft. (22.86 m), use cable made with 24Awg wiring, such as the P568-100-HD. (Lengths over 100-ft. (30.5 m) are available from Tripp Lite as a custom order) 24Awg HDMI cable is also needed when extending a 3D signal more than 50-ft. (15.24 m). A 3D signal can be extended up to 125-ft. (38.1 m) using 24Awg HDMI cable. Simply connect the longer cable between the source and the P166-001-A, and the shorter cable (16-ft. (4.88 m or less) between the adapter and the monitor. Software or drivers are not required. HDCP compliant.

Features

- Cleans up Home Theater installations by hiding HDMI Cables
- Wallplate is the size of a standard electrical outlet
- Extend a 1080p (24Hz) HDMI signal up to 150-ft. (45.72 m) from the source
- Use P568-Series HDMI cables in most applications
- When extending a 1080p (24Hz) signal more than 75-ft. (22.86 m), use cable made with 24Awg wiring, such as the P568-100-HD. (Lengths over 100-ft. (30.5 m) are available from Tripp Lite as a custom order)
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50-ft. (15.24 m). A 3D signal can be extended up to 125-ft. (38.1 m) using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- HDCP compliant
- No software or drivers required

Specifications

OVERVIEW	
UPC Code	037332141033





Product Type	Signal Booster	
Accessory Type	Wall Plate	
Technology	HDMI	
recinology	TIVIL	
VIDEO		
HDR Support	No	
3D Video Supported	No	
Maximum Signal Range (ft)	150	
Maximum Signal Range (m)	46	
INPUT		
Bus Powered	No	
POWER		
Power Over Cable (PoC) Support	No	
CONNECTIONS		
Side A - Connector 1	HDMI (FEMALE)	
Side B - Connector 1	HDMI (FEMALE)	
PHYSICAL		
Color	White	
Number of Displays	1	
Form Factor/Mounting Options	Wallplate	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Weight (lbs.)	0.14	
Shipping Weight (kg)	0.06	
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000	
COMMUNICATIONS		
EDID Compatible	No	
IR Remote Extension Support	No	
RS-232 Serial Extension Support	No	
Consumer Electronics Control (CEC) Supported	No	
USB Extension Support	No	
FEATURES & SPECIFICATIONS		





10/100 Ethernet Extension Support	No	
Built-In Equalizer	No	
Driver Required	No	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.