



3.5 mm 3-Position to 3.5 mm 4-Position Audio Headset Splitter Adapter Cable (2xF/M), 6 in. (15.2 cm)

MODEL NUMBER: P318-06N-MFF







Highlights

- Splits the 4-Position combo audio jack on your computer, laptop or mobile device into separate speaker and microphone jacks
- Allows for the connection of a set of speakers and microphone to a single 4-Position combo audio jack
- Molded cables with built-in strain relief

Package Includes

 6-in. 4-Position Male to (x2) 3-Position Female Audio Adapter Cable

Connect a set of speakers and microphone to the 4-position combo audio jack on your computer, laptop or mobile device

Features

- Splits the 4-Position combo audio jack on your computer, laptop or mobile device into separate speaker and microphone jacks
- Allows for the connection of a set of speakers and microphone to a single 4-Position combo audio jack
- Molded cables with built-in strain relief
- Constructed of 28AWG wire
- Features a compact design perfect for tucking into your laptop bag when you're on the go

Specifications

OVERVIEW		
UPC Code	037332184047	
Product Type	Passive Cable	
Technology	Stereo Audio	
Cable Type	Passive	
CONNECTIONS		
Side A - Connector 1	3.5MM (MALE)	
Side B - Connector 1	(2) 3.5MM (FEMALE)	
Latching or Gripping Connector	No	
PHYSICAL		





Color	Black	
Cable Jacket Color	Black	
Cable Length (ft.)	0.5	
Cable Length (m)	0.15	
Cable Length (in.)	6	
Cable Length (cm)	15.24	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Weight (lbs.)	0.08	
Shipping Weight (kg)	0.04	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.