

## VGA High-Resolution RGB Coaxial Cable (HD15 M/F), 10 ft. (3.05 m)

MODEL NUMBER: **P500-010**



Extend the high-resolution connection between your VGA-enabled computer and monitor up to 10 ft. with no ghosting. Recommended for easy access to VGA ports that are hidden or hard to reach.

### Description

The P500-010 VGA Coax High-Resolution Monitor Extension Cable (M/F) extends the connection between your VGA-enabled computer and monitor up to 10-ft. (3.05 m). It's recommended for easier access to VGA ports that are hidden under a desk or inside a cabinet or otherwise difficult to reach. Constructed from mini-coax (RGB) and paired video wire, it supports video resolutions up to 2048 x 1536, including 1080p, with no ghosting. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated HD15 connectors with gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

### Features

#### Extends Connection Between VGA-Enabled Computer and Monitor Up to 10-ft. (3.05 m)

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coax (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

## Specifications

OVERVIEW	
UPC Code	037332128096
Product Type	Passive Cable
Technology	Coax; VGA/SVGA

### Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coax (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

### System Requirements

- Display device with HD15 input

### Package Includes

- P500-010 VGA Coax High-Resolution Monitor Extension Cable (M/F), 10-ft. (3.05 m)



Powering Business Worldwide

TRIPP LITE  
SERIES

Cable Type	Passive
<b>CONNECTIONS</b>	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (FEMALE)
Latching or Gripping Connector	No
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.