

VGA Coax Monitor Extension Cable, Plenum Rated High Resolution Cable with RGB Coax (HD15 M/F), 100-ft.

MODEL NUMBER: P500-100-P



Highlights

- UL Listed, CMP rated cable
- Superior molded cables with foil and braid shielding for maximum EMI/RFI protection
- Constructed from 75ohm mini-coax (RGB) and paired video wire construction for superior signal quality
- Gold plated connectors and gold plated copper contacts

System Requirements

- Monitor with HD15 cable

Package Includes

- 100-ft. Plenum Rated XVGA/SVGA/VGA Monitor Extension Cable HD15M to HD15F Gold Connectors w/ RGB Coax

Description

Tripp Lite's Plenum Rated SVGA Extension cable is ideal in Educational or Commercial installations where local fire codes call for a CMP rated cable to run through walls, ceilings, and plenum air chambers. 100ft distance is achieved through high quality construction: 75ohm Coaxial conductors for Red, Green, and Blue (RGB) signals, each protected by a 93% tinned copper braid shield. An overall shield of Mylar foil and 85% Copper Braid shield ensures maximum signal integrity.

Features

- Superior molded cables with foil and braid shielding for maximum EMI/RFI protection
- UL Listed, CMP Rated Cable Jacket
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality
- Resolution supported for VGA, SVGA, XGA, SXGA, UXGA, QXGA
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 female molded connectors

Specifications

OVERVIEW	
UPC Code	037332129192
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (FEMALE)
Latching or Gripping Connector	No



Powering Business Worldwide



PHYSICAL	
Color	Black
Cable Length (ft.)	100
Cable Length (m)	30.49
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 3.00
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 7.62
Shipping Weight (lbs.)	2.90
Shipping Weight (kg)	1.32
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.