



# VGA Coax Monitor Easy Pull Extension Cable, High Resolution Cable with RGB Coax (HD15 M/F), 50 ft. (15.24 m)

MODEL NUMBER: P501-050



### **Highlights**

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- 75ohm mini-coax (RGB) and paired video wire construction delivers outstanding signal quality
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection

## **Package Includes**

- 50 ft. Male/Female Easy Pull SVGA/VGA Monitor Extension Cable w/ Connectors
- Wallplate with HD15 cutout

### **Features**

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior molded cables with foil and braid shielding for maximum EMI/RFI protection
- RGB 75-ohm coax construction for maximum video resolution
- HD15 male to HD15 female molded connectors
- Supports resolutions up to 1600 x 1200

# **Specifications**

OVERVIEW		
UPC Code	037332134639	
Technology	Coax; VGA/SVGA	
Cable Type	Passive	
CONNECTIONS		
Side A - Connector 1	HD15 (MALE)	
Side B - Connector 1	HD15 (FEMALE)	
Latching or Gripping Connector	No	
PHYSICAL		
Color	Black	





Cable Jacket Color	Black	
Cable Length (ft.)	50	
Cable Length (m)	15.24	
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 0.50	
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 1.27	
Shipping Weight (lbs.)	3.90	
Shipping Weight (kg)	1.77	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; EIA/ECA-310-E	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.