

VGA High-Resolution RGB Coaxial Cable (HD15 M/M), Right-Angle Connector, 3 ft. (0.91 m)

MODEL NUMBER: P502-003-RA



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 3 ft. apart with no ghosting.

Features

Allows Connection Between VGA-Enabled Computer and Monitor Up to 3 ft.

- Supports video resolutions up to 2048 x 1536, including 1080p
- Right-angle connector allows more room for connecting in tight spaces and moving connected equipment against a wall
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 male connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

Specifications

OVERVIEW	
UPC Code	037332147042
Product Type	Passive Cable
Technology	Coax; VGA/SVGA
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE) - RIGHT ANGLE
Side B - Connector 1	HD15 (MALE)

Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Right-angle HD15 connector easy to connect in tight spaces

System Requirements

- Display device with HD15 input
- Computer with HD15 output

Package Includes

- P502-003-RA VGA Coaxial High-Resolution Monitor Cable (M/M), 3 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.