

## VGA High-Resolution RGB Coaxial Cable (HD15 M/M), 25 ft. (7.62 m)

MODEL NUMBER: P502-025



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 25 ft. apart with no ghosting.

### Description

The P502-025 VGA Coaxial High-Resolution Monitor Cable (M/M) allows you to connect your VGA-enabled computer and monitor up to 25-ft. (7.62 m) apart. Constructed from mini-coaxial (RGB) and paired video wire, it supports video resolutions up to 2048 x 1536, including 1080p, with no ghosting. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated HD15 male connectors with gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

### Features

#### Allows Connection Between VGA-Enabled Computer and Monitor Up to 25-ft. (7.62 m)

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 male connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

## Specifications

OVERVIEW	
UPC Code	037332125286
Product Type	Passive Cable
Technology	Coax; VGA/SVGA
Cable Type	Passive

### Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

### System Requirements

- Display device with HD15 input
- Computer with HD15 output

### Package Includes

- P502-025 VGA Coaxial High-Resolution Monitor Cable (M/M), 25-ft. (7.62 m)



Powering Business Worldwide

TRIPP LITE  
SERIES

CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	25
Cable Length (m)	7.62
Cable Length (in.)	300
Shipping Dimensions (hwd / in.)	2.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	5.08 x 25.40 x 1.27
Shipping Weight (lbs.)	2.10
Shipping Weight (kg)	0.95
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	IEC/EN 60068-2-64; IEC/EN 60068; IEC/EN 62040
Product Compliance	RoHS; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.