



VGA High-Resolution RGB Coaxial Cable (HD15 M/M), 30 ft. (9.14 m)

MODEL NUMBER: P502-030



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 30 ft. apart with no ghosting.

Description

The P502-030 VGA Coaxial High-Resolution Monitor Cable (M/M) allows you to connect your VGAenabled computer and monitor up to 30-ft. (9.14 m) apart. Constructed from mini-coaxial (RGB) and paired video wire, it supports video resolutions up to 2048 x 1536, including 1080p, with no ghosting. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated HD15 male connectors with gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Features

- Allows Connection Between VGA-Enabled Computer and Monitor Up to 30-ft. (9.14 m)
- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- · Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 male connectors and contacts provide maximum conductivity and minimize data loss
- · Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

Specifications

OVERVIEW	
UPC Code	037332176530
Product Type	Passive Cable
Technology	Coax; VGA/SVGA
Cable Type	Passive

Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

System Requirements

- Display device with HD15 input
- Computer with HD15 output

Package Includes

 P502-030 VGA Coaxial High-Resolution Monitor Cable (M/M), 30-ft. (9.14 m)





CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	30
Cable Length (m)	9.15
Cable Length (in.)	360
Shipping Dimensions (hwd / in.)	10.00 x 12.00 x 1.00
Shipping Dimensions (hwd / cm)	25.40 x 30.48 x 2.54
Shipping Weight (lbs.)	1.50
Shipping Weight (kg)	0.68
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.