



VGA High-Resolution RGB Coaxial Cable (HD15 M/M), 100 ft. (30.5 m)

MODEL NUMBER: P502-100



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 100 ft. apart with no ghosting.

Description

The P502-100 VGA Coaxial High-Resolution Monitor Cable (M/M) allows you to connect your VGA-enabled computer and monitor up to 100-ft. (30.5 m) apart. Constructed from mini-coaxial (RGB) and paired video wire, it supports video resolutions up to 2048 x 1536, including 1080p, with no ghosting. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated HD15 male connectors with gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Features

Allows Connection Between VGA-Enabled Computer and Monitor Up to 100-ft. (30.5 m)

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- · Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 male connectors and contacts provide maximum conductivity and minimize data loss
- · Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

Specifications

OVERVIEW		
UPC Code	037332126702	
Product Type	Passive Cable	
Technology	Coax; VGA/SVGA	
Cable Type	Passive	

Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

System Requirements

- Display device with HD15 input
- Computer with HD15 output

Package Includes

 P502-100 VGA Coaxial High-Resolution Monitor Cable (M/M), 100-ft. (30.5 m)





CONNECTIONS			
Side A - Connector 1	HD15 (MALE)		
Side B - Connector 1	HD15 (MALE)		
Latching or Gripping Connector	No		
PHYSICAL			
Color	Black		
Cable Jacket Color	Black		
Cable Length (ft.)	100		
Cable Length (m)	30.49		
Cable Length (in.)	1200		
Shipping Dimensions (hwd / in.)	14.00 x 17.00 x 1.00		
Shipping Dimensions (hwd / cm)	35.56 x 43.18 x 2.54		
Shipping Weight (lbs.)	4.40		
Shipping Weight (kg)	2.00		
FEATURES & SPECIFICATIONS			
IP68 Rated	No		
IP20 Rated	No		
STANDARDS & COMPLIANCE			
Product Certifications	IEC/EN 60068-2-64; IEC/EN 60068; IEC/EN 62040		
Product Compliance	RoHS; CE (Europe); REACH		
WARRANTY & SUPPORT			
Product Warranty Period (Worldwide)	Lifetime limited warranty		

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.