



# Low-Profile High Resolution SVGA/VGA Monitor Cable with Audio and RGB Coaxial (HD15 M/M), 3 ft. (0.91 m)

## MODEL NUMBER: P504-003-SM



#### Description

This PVC, SVGA / VGA compact monitor replacement cable features a 40% reduced diameter, smaller molded connectors and built-in 3.5 mm stereo plugs for extending audio as well as video. The mini-coax (RGB) and paired video wire construction delivers superior video signal quality up to 2048 x 1536. Nickel-plated connectors and gold-plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high-density DB15 male connectors are molded and have integral strain relief to ensure long life.

#### **Features**

- Slim, compact SVGA / VGA Male Male Cable with Audio, 3-ft. (0.91 m)
- 40% thinner cable than standard VGA Cables
- Smaller, more compact, molded ends than standard VGA cables
- Supports up to 2048x1536 Resolution
- 22-inch Audio 3.5mm Stereo pigtails
- Foil and Braid shielded for superior noise suppression
- VW-1 Rated Jacketing

# **Specifications**

OVERVIEW	
UPC Code	037332163301
Product Type	Passive Cable
Technology	Coax; VGA/SVGA; Stereo Audio
Cable Type	Passive
CONNECTIONS	

### **Highlights**

- Slim, compact SVGA / VGA Male-Male Cable with Audio, 3ft. (0.91 m)
- 40% thinner cable than standard VGA Cables
- More compact molded ends
- Supports up to 2048x1536 Resolution
- VW-1 Rated Jacketing

#### **Package Includes**

3-ft. (0.91 m), Compact SVGA / VGA M/M Monitor Cable with Audio Cable





Side A - Connector 1	HD15 (MALE) - LOW PROFILE
Side A - Connector 2	3.5MM (MALE)
Side B - Connector 1	HD15 (MALE) - LOW PROFILE
Side B - Connector 2	3.5MM (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.17
Shipping Weight (kg)	0.08
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.