



VGA High-Resolution RGB Coaxial Cable with Audio (HD15 and 3.5mm M/M), 10 ft. (3.05 m)

MODEL NUMBER: P504-010





Highlights

- Superior molded cables with foilshielding for maximum EMI/RFI protection
- VW-1 and CM Rated Jacketing
- 3.5mm Stereo Plugs

Package Includes

 10-ft. SVGA/VGA Monitor Cable HD15M to HD15M w/Built-in Audio connectors

Features

- Extend both Video and Audio signals
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- HD15 male to HD15 male molded connectors
- Computer side Audio Pigtail: 8in Display side Audio Pigtail: 24in
- VW-1 and CM Rated Jacketing

Specifications

OVERVIEW		
UPC Code	037332135797	
Product Type	Passive Cable	
Technology	Coax; VGA/SVGA; Stereo Audio	
Cable Type	Passive	
CONNECTIONS		
CONNECTIONS		
Side A - Connector 1	HD15 (MALE)	
Side A - Connector 2	3.5MM (MALE)	
Side B - Connector 1	HD15 (MALE)	
Side B - Connector 2	3.5MM (MALE)	
Latching or Gripping Connector	No	





PHYSICAL		
Color	Black	
Cable Jacket Color	Black	
Cable Length (ft.)	10	
Cable Length (m)	3.05	
Cable Length (in.)	120	
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.50	
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 1.27	
Shipping Weight (lbs.)	0.80	
Shipping Weight (kg)	0.36	
Unit Dimensions (hwd / in.)	10.000 x 8.000 x 0.500	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks

are the property of their respective owners.