

# VGA Coax Monitor Cable with Audio, Plenum-Rated High Resolution Cable with RGB Coax (HD15 and 3.5mm M/M), 25-ft.

MODEL NUMBER: P504-025-P



### Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- CMP Plenum rated
- 3.5mm Stereo Plugs

### Package Includes

- 25-ft. Plenum SVGA/VGA Monitor Cable HD15M to HD15M w/Built-in Audio connectors

### Description

Tripp Lite's 25 foot Plenum SVGA/VGA monitor replacement cable features built-in 3.5mm stereo plugs, for extending audio as well video. The mini-coax (RGB) and paired video wire construction delivers superior video signal quality. Nickel plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure they last a long time. CMP rated jacket for areas that require plenum rated cables per local fire codes.

### Features

- Extend both Video and Audio signals
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Plenum rated jacket ( CMP )
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- HD15 male to HD15 male molded connectors
- Computer side Audio Pigtail: 8in Display side Audio Pigtail: 24in

## Specifications

OVERVIEW	
UPC Code	037332133182
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	3.5MM (MALE)
Side B - Connector 1	HD15 (MALE)



Powering Business Worldwide



Side B - Connector 2	3.5MM (MALE)
Latching or Gripping Connector	No
<b>PHYSICAL</b>	
Color	Black
Cable Length (ft.)	25
Cable Length (m)	7.62
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	2.00
Shipping Weight (kg)	0.91
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.