



# VGA Monitor Extension Cable, 640x480 (HD15 M/F), 25 ft. (7.62 m)

MODEL NUMBER: P510-025



# **Highlights**

 Superior molded cables with foilshielding for maximum EMI/RFI protection

## **System Requirements**

tyle="line-height:12px;margin-bottom:7px;">Monitor with HD15 cableand resolutions up to 640x480

# **Package Includes**

 25-ft. (7.62 m) VGA Monitor Extension Gold Cable HD15F to HD15M

## **Description**

VGA monitor extension cable will extend the reach of a monitor cable by an additional 25 feet (7.6 meters). Gold-plated connectors and gold-plated copper contacts ensure excellent conductivity. Shielded for maximum EMI/RFI protection. The HD15 male and HD15 female connectors are molded and have integral strain relief to ensure they last a long time.

For use with monitors with resolutions up to  $640 \times 480$  ( VGA Std ). For higher resolution monitors, please use P500-025.

## **Features**

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 female molded connectors

# **Specifications**

| OVERVIEW                       |               |  |
|--------------------------------|---------------|--|
| UPC Code                       | 037332123015  |  |
| Product Type                   | Passive Cable |  |
| Technology                     | VGA/SVGA      |  |
| Cable Type                     | Passive       |  |
| CONNECTIONS                    |               |  |
| Side A - Connector 1           | HD15 (MALE)   |  |
| Side B - Connector 1           | HD15 (FEMALE) |  |
| Latching or Gripping Connector | No            |  |





| PHYSICAL                               |                           |
|--|---------------------------|
| Color                                  | Black                     |
| Cable Jacket Color                     | Black                     |
| Cable Length (ft.)                     | 25                        |
| Cable Length (m)                       | 7.62                      |
| Cable Length (in.)                     | 300                       |
| Shipping Dimensions (hwd / in.)        | 8.50 x 6.90 x 0.50        |
| Shipping Dimensions (hwd / cm)         | 21.59 x 17.53 x 1.27      |
| Shipping Weight (lbs.)                 | 0.80                      |
| Shipping Weight (kg)                   | 0.36                      |
| FEATURES & SPECIFICATIONS              |                           |
| IP68 Rated                             | No                        |
| STANDARDS & COMPLIANCE                 |                           |
| Product Compliance                     | RoHS                      |
| WARRANTY & SUPPORT                     |                           |
| Product Warranty Period<br>(Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.