

VGA Monitor Cable, 640x480 (HD15 M/M), 15 ft. (4.57 m)

MODEL NUMBER: P512-015



Description

This VGA monitor replacement cable is designed for use with a monitor that has a removable cable with HD15 connectors. This 15-foot (4.6-meter) cable has gold-plated connectors and gold-plated copper contacts to ensure excellent conductivity. Shielded for maximum EMI/RFI protection. The HD15 male connectors are molded and have integral strain relief to ensure they last a long time. For use with monitors with resolutions up to 640 x 480. For higher resolution monitors, see P502-015.

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 male molded connectors

Specifications

OVERVIEW	
UPC Code	037332182494
Product Type	Passive Cable
Technology	VGA/SVGA
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (MALE)
Latching or Gripping Connector	No
PHYSICAL	

Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection

System Requirements

- Monitor with removable HD15 cable and resolutions up to 640x480.

Package Includes

- 15-ft. (4.57 m) VGA Monitor Cable HD15M to HD15M Gold Connectors



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	15
Cable Length (m)	4.57
Cable Length (in.)	180
Shipping Dimensions (hwd / in.)	0.50 x 5.80 x 6.60
Shipping Dimensions (hwd / cm)	1.27 x 14.73 x 16.76
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.