

Serial DB9 Serial Extension Cable, Straight Through (DB9 M/F), 6 ft. (1.83 m)

MODEL NUMBER: P520-006



Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection

Package Includes

- 6-ft. (1.83 m) RS-232 Serial Extension DB9F to DB9M

Description

This extends an RS-232 Serial cable by an additional six feet (1.8 meters). Foil-shielding construction provides maximum EMI/RFI protection. The DB9 female and DB9 male connectors are molded with built-in strain relief to ensure that the cable lasts a long time.

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- DB9 (male) to DB9 (female)

Specifications

OVERVIEW	
UPC Code	037332012388
Technology	Serial
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	DB9 (MALE)
Side B - Connector 1	DB9 (FEMALE)
PHYSICAL	
Color	Gray
Cable Jacket Color	Gray
Cable Length (ft.)	6



Powering Business Worldwide



Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Relative Humidity	0% -90%, Non-condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.