

DVI Dual Link Cable with Audio, Digital TMDS Monitor Cable (DVI-D and 3.5mm M/M), 6 ft. (1.83 m)

MODEL NUMBER: P560-006-A



Description

This DVI Dual-Link TMDS cable delivers the high performance and high bandwidth needed for today's digital video displays. In addition, built-in 3.5 mm stereo connectors allow simultaneous connection to your computer's stereo output to either built-in monitor speakers or external speakers. Gold-plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Dual Link. Both DVI connectors are molded and have integral strain relief for long life reliability.

Features

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- 3.5MM Stereo connection molded into the assembly
- Dual Link digital signaling for transmission speeds to 9.9Gbps and 2560x1600 Resolution
- Gold plated copper contacts ensure excellent conductivity
- Meets DVI DDWG Standard
- PC and Mac compatible
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors

Specifications

OVERVIEW	
UPC Code	037332141002
Product Type	Passive Cable
Technology	DVI; Stereo Audio
Cable Type	Passive
CONNECTIONS	

Highlights

- For use with Dual or Single TMDS Link specified equipment
- Molded in 3.5mm Stereo connectors
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

- Monitor with DVI, and CPU with Dual Link DVI capabilities
- Stereo jack on computer, stereo jack on monitor or external speakers

Package Includes

- 6-ft. (1.83 m) DVI Dual Link TMDS cable w/Audio - DVI-D, M/M 3.5mm, M/M



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side A - Connector 2	3.5MM (MALE)
Side B - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 2	3.5MM (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	0.50 x 6.00 x 6.00
Shipping Dimensions (hwd / cm)	1.27 x 15.24 x 15.24
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.