

## DVI Dual Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 25 ft. (7.62 m)

MODEL NUMBER: P560-025



### Description

This DVI Dual-Link TMDS cable delivers the high performance and high bandwidth needed for today's digital video displays. Note: Review your monitor manufacturer's specifications for a stated maximum DVI cable length. While many monitors only support a five-meter (16-foot) DVI cable, simply adding a B120-000 DVI Extender will guarantee full digital signal strength at any length up to 150 feet (45.7 meters). Gold-plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Dual or Single Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars drain off extraneous electrical interference.

### Features

- Superior molded cables with foil/braid shielding for maximum EMI/RFI
- Dual Link digital signaling for transmission speeds to 9.9Gbps and 2560 x 1600 resolution
- Meets DVI DDWG Standard
- PC and Mac compatible
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors
- Check monitor manufacturers cable length specs - may need B120-000 DVI Extender

## Specifications

| OVERVIEW     |               |
|--------------|---------------|
| UPC Code     | 037332138804  |
| Product Type | Passive Cable |
| Technology   | DVI           |
| Cable Type   | Passive       |
| CONNECTIONS  |               |

### Highlights

- For use with Dual or Single TMDS Link specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Check monitor manufacturers cable length specs - may need B120-000 DVI Extender

### System Requirements

- Monitor with DVI, and CPU with Dual or Single Link DVI capabilities

### Package Includes

- DVI Dual Link TMDS cable - DVI-D, M/M, 25-ft. (7.62 m)



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                           |
|--------------------------------------|---------------------------|
| Side A - Connector 1                 | DVI-D DUAL LINK (MALE)    |
| Side B - Connector 1                 | DVI-D DUAL LINK (MALE)    |
| Latching or Gripping Connector       | No                        |
| <b>PHYSICAL</b>                      |                           |
| Color                                | Black                     |
| Cable Jacket Color                   | Black                     |
| Cable Length (ft.)                   | 25                        |
| Cable Length (m)                     | 7.62                      |
| Cable Length (in.)                   | 300                       |
| Shipping Dimensions (hwd / in.)      | 12.00 x 10.00 x 0.50      |
| Shipping Dimensions (hwd / cm)       | 30.48 x 25.40 x 1.27      |
| Shipping Weight (lbs.)               | 1.43                      |
| Shipping Weight (kg)                 | 0.65                      |
| Unit Dimensions (hwd / in.)          | 12.000 x 10.000 x 0.500   |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                           |
| IP68 Rated                           | No                        |
| IP20 Rated                           | No                        |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                           |
| Product Compliance                   | RoHS                      |
| <b>WARRANTY &amp; SUPPORT</b>        |                           |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.