

Signal Booster Strength

In some applications, a signal booster (Model Number: B120-000) will need to be used with this cable to ensure a signal strong enough for your display.

DVI High Definition Dual Link Digital TMDS Monitor Cable (DVI-D M/M), 100 ft. (30.5 m)

MODEL NUMBER: P560-100-HD



Description

This High-Definition DVI Dual-Link TMDS cable delivers the high performance and high bandwidth needed for today's digital video displays. 24 AWG wire and gold-plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Dual Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars to drain off extraneous electrical interference. In most applications, a signal booster (B120-000) will need to be used with this cable to ensure a signal strong enough for your display.

Features

- 24AWG High Definition Cable
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Dual Link digital signalling for transmission speeds to 9.9Gbps
- Meets DVI DDWG Standard
- PC and Mac compatible
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projector
- In most applications, a signal booster (B120-000) will need to be used with this cable to ensure a signal strong enough for your display.

Highlights

- 24AWG High Definition Cable
- For use with Dual TMDS Link specified video cards
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

- DVI monitor and computer

Package Includes

- 100-ft. (30.5 m) DVI High Definition Dual Link TMDS Cable (DVI-D M/M)

Specifications

OVERVIEW	
UPC Code	037332177872
Product Type	Passive Cable



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	DVI
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 1	DVI-D DUAL LINK (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	100
Cable Length (m)	30.49
Cable Length (in.)	1200
Shipping Dimensions (hwd / in.)	5.00 x 10.70 x 15.00
Shipping Dimensions (hwd / cm)	12.70 x 27.18 x 38.10
Shipping Weight (lbs.)	9.50
Shipping Weight (kg)	4.31
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.