



Signal Booster Strength

In some applications, a signal booster (B120-000-SL) should be used with this cable to ensure a signal strong enough for your display. An alternate solution is to use a DVI over Cat5 Extender (B140-101X) in place of a 50-foot DVI cable and signal booster.

DVI Single Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 50 ft. (15.24 m)

MODEL NUMBER: P561-050



Features

- For use with Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 1920 x 1200
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- In most applications, a signal booster (B120-000-SL) will need to be used with this cable to ensure a signal strong enough for your display

Specifications

OVERVIEW	
UPC Code	037332130877
Product Type	Passive Cable
Technology	DVI
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	DVI-D SINGLE LINK (MALE)

Highlights

- For use with Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 1920 x 1200
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

DVI monitor and computer

Package Includes

 50-ft. DVI Single Link TMDS Cable (DVI-D M/M)





Side B - Connector 1	DVI-D SINGLE LINK (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	50
Cable Length (m)	15.24
Cable Length (in.)	600
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 1.00
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 2.54
Shipping Weight (lbs.)	2.70
Shipping Weight (kg)	1.22
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.