



#### Signal Booster Strength

In some applications, a signal booster (B120-000-SL) should be used with this cable to ensure a signal strong enough for your display. An alternate solution is to use a DVI over Cat5 Extender (B140-101X) in place of a 75-foot DVI cable and signal booster.

## DVI Single Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 75 ft. (22.86 m)

### MODEL NUMBER: P561-075



#### Description

This DVI Single-Link TMDS cable delivers the high performance and high bandwidth needed for today's digital video displays. Gold-plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Single Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars to drain off extraneous electrical interference. In most applications, a signal booster (B120-000-SL) will need to be used with this cable to ensure a signal strong enough for your display.

#### **Features**

- For use with Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 1920 x 1200
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- In most applications, a signal booster (B120-000-SL) will need to be used with this cable to ensure a signal strong enough for your display

# **Specifications**

OVERVIEW	
UPC Code	037332168580
Product Type	Passive Cable

#### **Highlights**

- For use with Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 1920 x 1200
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

#### **System Requirements**

DVI monitor and computer

#### **Package Includes**

 75-ft. (22.86 m) DVI Single Link TMDS Cable (DVI-D M/M)





Technology	DVI
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	DVI-D SINGLE LINK (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	75
Cable Length (m)	22.87
Cable Length (in.)	900
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 1.00
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 2.54
Shipping Weight (lbs.)	3.20
Shipping Weight (kg)	1.45
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.