



DVI Y Splitter Cable, Digital Monitors (DVI-D M to 2x F), 1 ft. (0.31 m)

MODEL NUMBER: P564-001







Features

- DVI-D Male to 2 x DVI-D Female, 1 ft.
- Inexpensive solution for presentations
- Supports video resolutions up to 1920 x 1080
- Molded, double-shielded construction for maximum EMI/RFI protection
- Two monitors display the same image from one PC
- The P564-001 is designed for two DVI-D monitors to be connected at the same time. If only one monitor is connected, and the other DVI-D Female port left open, video quality will be negatively affected

Highlights

- Splits the digital (DVI) signal providing simultaneous display of the same image on two DVI monitors
- DVI-D male splits to two (2) DVI-D females
- Supports video resolutions up to 1920 x 1080

System Requirements

- DVI-D or DVI-I Female PC Card Connector, and DVI Enabled Monitors
- The P564-001 is designed for two DVI-D monitors to be connected at the same time. If only one monitor is connected, and the other DVI-D Female port left open, video quality will be negatively affected

Package Includes

 DVI-D Male to (2) DVI-D Female Cable - 1 ft.

Specifications

OVERVIEW		
OVERVIEW.		
UPC Code	037332138798	
Product Type	Splitter	
Technology	DVI	
Host Connector	DVI-D DUAL LINK (MALE)	
Cable Type	Passive	
CONNECTIONS		
Side A - Connector 1	DVI-D DUAL LINK (MALE)	
Side B - Connector 1	(2) DVI-D DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)	
Latching or Gripping Connector	No	
Input x Output	1 x 2	





Daisy-chainable / Cascadable	No	
PHYSICAL		
Color	Black	
Cable Jacket Color	Black	
Cable Length (ft.)	1	
Cable Length (m)	0.30	
Cable Length (in.)	12	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.22	
Shipping Weight (kg)	0.10	
FEATURES & SPECIFICATIONS		
MST Support	No	
IP68 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.