



HDMI to DVI Adapter Cable (M/M), 10 ft. (3.1 m)

MODEL NUMBER: P566-010











Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and DVI-enabled display.

Description

This HDMI - DVI cable allows interconnection between digital display devices, such as HDTVs and projectors, to digital source devices, such as Set-Top boxes, DVD/DVD-R players and AV receivers. HDMI DTVs will display video received from existing DVI-equipped products, and DVI-equipped TVs will display video from HDMI sources. HDMI technology uses a much more compact and user-friendly connector than the existing DVI connector. The HDMI specification handles higher bandwidth, uncompressed video, and multi-channel digital audio, all in one neat cable solution. (HDMI-DVI cable supports digital video only and does not support audio.)

Features

- 10-ft. (3.05 m) HDMI to DVI-D Single Link Adapter Cable
- Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and a DVI-enabled display.
- · Gold plated connectors and contacts provide optimal signal transfer
- Premium Double-Shielded HDMI compliant cable protects against outside noise (EMI/RFI)
- Impedance matched twisted pair construction reduces cross-talk and interference
- Supports High-Definition (HD) video resolutions up to 1920 x 1080 @60Hz (1080p).

Specifications

OVERVIEW	
UPC Code	037332122940
Product Type	Passive Cable
Technology	DVI; HDMI
VIDEO	
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)

Highlights

- Premium double shielded digital video cable protects against EMI/RFI noise.
- Gold plated connectors and contacts provide optimal signal transfer.
- Supports high-def video resolutions up to 1920 x 1080 @60Hz (1080p).
- Supports a bandwidth up to 5Gbps
- This product is covered by a Lifetime Limited Warranty

Package Includes

 10-ft. (3.05 m) HDMI to DVI Gold Digital Video Cable -HDMI-M/DVI-M





CONNECTIONS		
Side A - Connector 1	HDMI (MALE)	
Side B - Connector 1	DVI-D SINGLE LINK (MALE)	
Connector Plating	Gold	
Contact Plating	Gold	
PHYSICAL		
Color	Black	
Material of Construction	PVC	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	5.5mm	
Wire Gauge (AWG)	30	
Cable Length (ft.)	10	
Cable Length (m)	3.05	
Cable Length (in.)	120	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.33	
Shipping Weight (kg)	0.15	
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500	
Unit Packaging Type	Polybag	
ENVIRONMENTAL		
Operating Temperature Range	32° to 113°F (0° to 45°C)	
Storage Temperature Range	14° to 158°F (-10° to 70°C)	
Operating Humidity Range	10% to 85% RH, Non-Condensing	
Storage Humidity Range	5% to 90% RH, Non-Condensing	
FEATURES & SPECIFICATIONS		
HDCP Specification	1.3	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		





Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.