

In some applications where the HDMI cable exceeds 16ft, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display.

HDMI Easy Pull Cable, Digital Video with Audio (M/M), 25 ft.

MODEL NUMBER: **P568-025-EZ**



Highlights

- 2-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- Bandwidth up to 10.2 Gbps - Full 1080p resolution
- Supports High Definition (HD) video resolutions up to 1080p

Package Includes

HDMI Easy Pull Cable, HD 1080p, Digital Video with Audio (M/M), 25 ft.

Description

Tripp Lite's 25-foot (7.6-meter) HDMI Easy Pull Monitor Cable w/ Connectors makes running long video cables a snap. The pull-apart design allows the cable to run through conduit or other tight areas that a HDMI connector wouldn't fit through. Diameter of the circular DIN end is only 7/8 inch. Circular Easy Pull connector is threaded to ensure maximum security once the cable is reattached. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both HDMI male ends are molded and have integral strain relief to provide long life. UL20276 Digital Video Cable supports 1080p. In most applications, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display.

Features

- 2-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- High quality quad-shielded cable with gold connectors and pins
- Bandwidth up to 10.2 Gbps - Full 1080p resolution as specified by HDMI 1.2
- In most applications where the HDMI cable exceeds 16 ft., a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display
- HDMI male to male molded connectors
- UL20276 Digital Video Cable
- Supports High Definition (HD) video resolutions up to 1080p

Specifications

OVERVIEW



Powering Business Worldwide



UPC Code	037332175564
Technology	HDMI
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	1920 x 1080 @ 60Hz
Max Supported Color Depth	48-bit Deep Color
HDR Support	No
3D Video Supported	No
Chroma Sub Sampling	4:4:4
EDID Support	Yes
Signal Transmission	Bidirectional
AUDIO	
Audio Specification	DTS-HD
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	DIN 19 PIN (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	0
PHYSICAL	
Color	Black
Material of Construction	PVC
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	6.5 mm
Wire Gauge (AWG)	28
Cable Length (ft.)	25
Cable Length (m)	7.62



Powering Business Worldwide



Ferrite Core	No
Minimum Bend Radius	32.5mm
Shipping Dimensions (hwd / in.)	1.00 x 6.90 x 8.80
Shipping Dimensions (hwd / cm)	2.54 x 17.53 x 22.35
Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
FEATURES & SPECIFICATIONS	
EMI/RFI Line Noise Protection	No
MST Support	No
Antibacterial	No
IP68 Rated	No
IP20 Rated	No
Armored Cable	No
Ethernet Support	No
HDCP Specification	1.4; 2.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.