



Signal Booster Strength

In some applications, a signal booster (B122-000-60) should be used with this cable to ensure a signal strong enough for your display. An alternate solution is to use a HDMI over Cat5 Extender (B126-1A1) in place of a 50-foot HDMI cable and signal booster.

Standard-Speed HDMI Plenum Rated Cable, Digital Video with Audio (M/M), 50 ft. (15.24 m)

MODEL NUMBER: P568-050-P



Features

- · Plenum-rated for use where local code calls for a fire resistant cable
- Creates a pure digital connection between HDMI-enabled HDTV display devices and HDMI-enabled digital video sources
- Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- · Gold-plated connectors provide optimal signal transfer
- · Premium double-shielded cable protects against outside noise (EMI/RFI)
- · Impedance-matched twisted-pair construction reduces cross-talk and interference
- · Bandwidth up to 10.2 Gbps Full 1080p resolution
- In most applications, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display

Specifications

OVERVIEW	
UPC Code	037332149985
Product Type	Passive Cable
Technology	HDMI
Cable Type	Passive

Highlights

- Plenum-rated for use where local code calls for a fire resistant cable
- Premium double-shielded digital audio/video cable
- Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- Gold-plated connectors provide optimal signal transfer
- Bandwidth up to 10.2 Gbps -Full 1080p resolution
- Standard Speed HDMI and HDCP compliant
- Supports HD Video resolutions up to 1080p

Package Includes

 Standard Speed HDMI Plenum Rated Cable, 1080p, Digital Video with Audio (M/M), 50-ft.





VIDEO			
Max Supported Video Resolution	1920 x 1200 (1080p)		
Max Supported Color Depth	48-bit Deep Color		
HDR Support	No		
3D Video Supported	No		
Chroma Sub Sampling	4:4:4		
EDID Support	Yes		
Signal Transmission	Bidirectional		
AUDIO			
Audio Specification	DTS-HD		
CONNECTIONS			
Side A - Connector 1	HDMI (MALE)		
Side B - Connector 1	HDMI (MALE)		
Connector Plating	Gold		
Contact Plating	Gold		
Connector Style	Straight		
Latching or Gripping Connector	No		
USER INTERFACE, ALERTS & COM	USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	0		
PHYSICAL			
Color	Black		
Material of Construction	PVC		
Cable Jacket Color	Black		
Connector Color	Black		
Cable Jacket Material	PVC		
Cable Jacket Rating	СМР		
Cable Outer Diameter (OD)	10.0 mm		
Wire Gauge (AWG)	24		
Cable Length (ft.)	50		
Cable Length (m)	15.24		
Cable Length (in.)	600		
Ferrite Core	No		
Minimum Bend Radius	50mm		





Shipping Dimensions (hwd / in.)	14.00 x 17.00 x 1.00
Shipping Dimensions (hwd / cm)	35.56 x 43.18 x 2.54
Shipping Weight (lbs.)	5.30
Shipping Weight (kg)	2.40
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
FEATURES & SPECIFICATIONS	
EMI/RFI Line Noise Protection	No
MST Support	No
Antibacterial	No
IP68 Rated	No
IP20 Rated	No
Armored Cable	No
Ethernet Support	No
Fire Rating	Plenum Rated
HDCP Specification	1.4; 2.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.