



High Speed HDMI Cable with Ethernet, UHD 4K, Digital Video with Audio (M/M), 10 ft. (3.05 m)

MODEL NUMBER: P569-010









Highlights

- 10-ft. (3.05 m) High Speed with Ethernet HDMI cable v1.4
- Supports transmission speeds up to 18 Gbps
- Backward compatible to previous HDMI generations
- Video mirroring with iPad2

System Requirements

 HDMI video source and HDMI enabled TV / Monitor

Package Includes

• 10-ft. (3.05 m) High Speed with Ethernet HDMI Cable v1.4

Features

- 10-ft. (3.05 m) High Speed with Ethernet HDMI cable v1.4
- Supports transmission speeds up to 18 Gbps
- Backward compatible to previous HDMI generations
- Fully molded cables, with Gold plated connectors assures long life
- Perfect for connecting an iPad2 to an HDTV (video mirroring) to watch movies, play games, surf the web and display presentations

Specifications

OVERVIEW		
UPC Code	037332160690	
Product Type	Passive Cable	
Technology	HDMI	
Cable Type	Passive	
VIDEO		
Max Supported Video Resolution	3840 x 2160 (4K) @ 30Hz	
Max Supported Color Depth	24-bit True Color	
HDR Support	No	
3D Video Supported	Yes	
Chroma Sub Sampling	4:4:4	
EDID Support	Yes	





Signal Transmission	Bidirectional	
<u> </u>		
AUDIO		
Audio Specification	Stereo Audio	
CONNECTIONS		
Side A - Connector 1	HDMI (MALE)	
Side B - Connector 1	HDMI (MALE)	
Connector Plating	Gold	
Contact Plating	Gold	
Connector Style	Straight	
Latching or Gripping Connector	No	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	0	
PHYSICAL		
Color	Black	
Cable Jacket Color	Black	
Connector Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	6.0 mm	
Wire Gauge (AWG)	28	
Cable Length (ft.)	10	
Cable Length (m)	3.05	
Cable Length (in.)	120	
Ferrite Core	No	
Minimum Bend Radius	60mm	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Weight (lbs.)	0.35	
Shipping Weight (kg)	0.16	
ENVIRONMENTAL		
Operating Temperature Range	32° to 113°F (0° to 45°C)	
Storage Temperature Range	-40° to 176°F (-40° to 80°C)	
Operating Humidity Range	10% to 85% RH, Non-Condensing	





Storage Humidity Range	5% to 90% RH, Non-Condensing	
COMMUNICATIONS		
Consumer Electronics Control (CEC) Supported	Yes	
FEATURES & SPECIFICATIONS		
EMI/RFI Line Noise Protection	No	
MST Support	No	
Antibacterial	No	
IP68 Rated	No	
IP20 Rated	No	
Armored Cable	No	
Ethernet Support	Yes	
HDCP Specification	1.4	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; REACH	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.