

# DMS-59 to Dual VGA Splitter Y Cable (M to 2xF), 1 ft. (0.31 m)

MODEL NUMBER: P574-001



### Highlights

- Attach two VGA enabled monitors to your DMS59 Graphics card
- Superior molded connectors for long life use

### Package Includes

DMS59 to (2) VGA Female Splitter Cable - 1-ft. (0.31 m)

### Features

- LFH59 (DMS59) to 2 x VGA Female, 1-ft. (0.31 m)
- Compatible with most DMS-59 video cards including nVidia, Matrox, HP, PNY, and ATI
- Rugged molded construction and gold plated contacts

## Specifications

OVERVIEW	
UPC Code	037332145987
Product Type	Splitter
Technology	VGA/SVGA
Host Connector	DMS59 (MALE)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	DMS59 (MALE)
Side B - Connector 1	(2) HD15 (FEMALE)
Latching or Gripping Connector	No
Input x Output	1 x 2
Daisy-chainable / Cascadable	No
PHYSICAL	
Color	Black



Powering Business Worldwide



Cable Jacket Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Shipping Dimensions (hwd / in.)	11.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	27.94 x 17.78 x 1.27
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
<b>FEATURES &amp; SPECIFICATIONS</b>	
MST Support	No
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.