



Signal Booster Strength

In some applications, a signal booster (Model Number: B121-000) should be used with this cable to ensure a signal strong enough for your display.

DisplayPort Cable with Latches (M/M) 100 ft. (30.5 m)

MODEL NUMBER: P580-100



Highlights

- Digital Video and Audio in one cable
- Supports 1080p resolution
- Small footprint compared to VGA or DVI

Package Includes

DisplayPort Monitor Cable - 100-ft. (30.5 m)

Features

- The future standard for Digital Video and Audio connections
- Supports Displayport v1.2
- Provides up to 1080p resolution
- Monitor Resolution Support: 2560x1600 @ 60Hz, 1920x1200 @ 120Hz
- Supports High Definition Content Protection (HDCP)
- In most applications, a signal booster (B121-000) should be used with this cable to ensure a signal strong enough for your display.

Specifications

OVERVIEW		
UPC Code	037332176585	
Product Type	Passive Cable	
Technology	DisplayPort	
Cable Type	Passive	
VIDEO		
VIDEO		
Max Supported Video Resolution	1920 x 1200 (1080p)	





CONNECTIONS		
Side A - Connector 1	DISPLAYPORT (MALE)	
Side B - Connector 1	DISPLAYPORT (MALE)	
Latching or Gripping Connector	Yes	
PHYSICAL		
Color	Black	
Cable Jacket Color	Black	
Cable Length (ft.)	100	
Cable Length (m)	30.49	
Cable Length (in.)	1200	
Shipping Dimensions (hwd / in.)	14.00 x 17.00 x 1.00	
Shipping Dimensions (hwd / cm)	35.56 x 43.18 x 2.54	
Shipping Weight (lbs.)	3.60	
Shipping Weight (kg)	1.63	
FEATURES & SPECIFICATIONS		
IP68 Rated	No No	
STANDARDS & COMPLIANCE		
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.