



DisplayPort to DVI Adapter Cable (DP with Latches to DVI-D Single Link M/M), 10 ft. (3.1 m)

MODEL NUMBER: P581-010











Highlights

- Displayport Male to DVI-D Male, 10-ft. (3.05 m)
- Molded ends
- 1080p Resolution
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dualmode port

System Requirements

 Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P581-006-V2

Package Includes

 10-ft. (3.05 m) DisplayPort to DVI Single link Cable M/M

Description

The P581-010 DisplayPort Male to DVI-D Male Cable allows you to connect a computer with a DisplayPort connection to a HDTV or monitor with a DVI connection. Digital video signals are passed through with full 1080p video resolution supported. Fully molded ends ensure long life enjoyment. The P581-010 is a passive adapter and requires the host computer's DisplayPort to be DP++ (DisplayPort ++), which allows HDMI and DVI signals to be passed through. Check your computer's documentation for compatibility.

Features

- Displayport Male to DVI-D Male, 10-ft. (3.05 m)
- Allows PC images to be dispalyed on big screen HDTV or computer monitors with DVI
- Molded ends
- 1080p Resolution
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port

Specifications

OVERVIEW	
UPC Code	037332153227
Product Type	Passive Cable
Technology	DVI; DisplayPort
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)





DISPLAYPORT (MALE)	
DVI-D SINGLE LINK (MALE)	
Nickel	
Gold	
PHYSICAL	
Black	
Black	
PVC	
VW-1	
6	
1.83	
72	
9.00 x 7.00 x 0.50	
22.86 x 17.78 x 1.27	
0.46	
0.21	
ENVIRONMENTAL	
32° to 158°F (0° to 70°C)	
14° to 158°F (-10° to 70°C)	
10% to 85% RH, Non-Condensing	
5% to 90% RH, Non-Condensing	
FEATURES & SPECIFICATIONS	
1.2	
STANDARDS & COMPLIANCE	
RoHS	
WARRANTY & SUPPORT	
3-year limited warranty	





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.