

## DisplayPort to HDMI Adapter Cable (M/M), 6 ft. (1.8 m)

MODEL NUMBER: P582-006



Connect a computer with DisplayPort to a HDMI-enabled TV

### Features

- 6ft DisplayPort to HDMI Adapter cable
- Supports 1080P video, as well as audio ( if video card enabled )
- HDCP compatible
- In-line Passive adapter
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++ ) dual-mode port

## Specifications

| OVERVIEW                       |                     |
|--------------------------------|---------------------|
| UPC Code                       | 037332148049        |
| Product Type                   | Passive Cable       |
| Technology                     | HDMI; DisplayPort   |
| Cable Type                     | Passive             |
| VIDEO                          |                     |
| Max Supported Video Resolution | 1920 x 1200 (1080p) |
| CONNECTIONS                    |                     |
| Side A - Connector 1           | DISPLAYPORT (MALE)  |
| Side B - Connector 1           | HDMI (MALE)         |

### Highlights

- Supports 1080p 1920 x 1080 resolution
- Supports Audio
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++ ) dual-mode port

### System Requirements

- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P582-006-V2

### Package Includes

- 6-ft. (1.83 m) DisplayPort to HDMI Adapter cable



Powering Business Worldwide

TRIPP LITE  
SERIES

| PHYSICAL                            |                            |
|-------------------------------------|----------------------------|
| Color                               | Black                      |
| Cable Jacket Color                  | Black                      |
| Cable Jacket Material               | PVC                        |
| Cable Jacket Rating                 | VW-1                       |
| Cable Outer Diameter (OD)           | 6.5mm                      |
| Wire Gauge (AWG)                    | 28                         |
| Cable Length (ft.)                  | 6                          |
| Cable Length (m)                    | 1.83                       |
| Cable Length (in.)                  | 72                         |
| Shipping Dimensions (hwd / in.)     | 9.00 x 7.00 x 0.50         |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.78 x 1.27       |
| Shipping Weight (lbs.)              | 0.25                       |
| Shipping Weight (kg)                | 0.11                       |
| STANDARDS & COMPLIANCE              |                            |
| Product Compliance                  | Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT                  |                            |
| Product Warranty Period (Worldwide) | 3-year limited warranty    |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.